Model CHF5

Tyvek® 500 Xpert

DuPont[™] Tyvek® 500 Xpert/DuPont[™] Tyvek® 500 Xpert (EcoPack). Hooded coverall. Ergonomic-protective design. Stitched external seams. Elasticated wrists, ankles and face. Elasticated waist (glued-in). Tyvek® zipper and flap. Eco Pack available. White.

Name	Description
Full Part Number	TYCHF5SWHXP/TYCHF5SWHXB
Fabric/Materials	Tyvek®
Design	Hooded coverall with elastics
Seam	Stitched (external)
Color	White
Sizes	SM, MD, LG, XL, 2X, 3X, 4X, 5X, 6X, 7X
Quantity/Box	100 per box, individually packed 100 per box, 4 units of 25 (Eco Pack)

FEATURES & PRODUCT DETAILS

DuPont[™] Tyvek® 500 Xpert/DuPont[™] Tyvek® 500 Xpert (Ecopack). Hooded coverall available in white, in sizes SM to 3X (blue and green garments also available). Robust yet lightweight (<180g per garment). 3-piece hood for optimal fit to head and face when turning. Elasticated face, wrists and ankles as well as glued-in waist elastic. Ample crotch area for freedom of movement. Large, easy-to-grasp zipper puller.

Tyvek® garments are composed of flash spun high density polyethylene, providing an ideal balance of protection, durability and comfort. Tyvek® is permeable to both air and water vapour, yet repels water-based liquids and aerosols. It offers an excellent barrier against fine particles and fibres (down to 1 micron in size), is ultra-low-linting and antistatically treated. Silicon non-added. Applications for Tyvek® 500 Xpert garments include those found in pharmaceutical handling, chemical processing, the oil and gas industry, general maintenance and operations, automatic spray painting and many others.

- Certified according to Regulation (EU) 2016/425.
- Chemical protective clothing, Category III, Type 5-B and 6-B.
- EN 14126 (barrier to infective agents), EN 1073-2 (protection against radioactive contamination)..
- Antistatic treatment (EN 1149-5) on both sides.
- Stitched external seams.
- Very low inward leakage thanks to optimised design.
- Tyvek® auto-lock zipper and zipper flap for increased protection..

ADDITIONAL EQUIPMENT NEEDED

- Please read, understand and follow the Instructions For Use
- Wear other appropriate PPE such as, but not limited to, respiratory, eye, head, hand, and foot protection based on the hazard assessment.

SIZES

Article Number	Additional info	Product Size
D14663953	MTS	SM
D14663967	MTS	MD
D14663977	MTS	LG
D14663986	MTS	XL
D14663997	MTS	2X
D14664003	MTS	3X
D15553613	МТО	4X
D15553614	МТО	5X
D15553615	МТО	6X
D15553616	МТО	7X
D15359234	Eco Pack,MTS	SM
D15359243	Eco Pack,MTS	MD
D15359254	Eco Pack,MTS	LG
D15359261	Eco Pack,MTS	XL
D15359276	Eco Pack,MTS	2X
D15359284	Eco Pack,MTS	3X

Physical Properties



Data relating to mechanical performance of the fabrics used in DuPont chemical protective clothing, listed for the selected garment according to the test methods and relevant European standard, if applicable. Such properties, including abrasion and flex-cracking resistance, tensile strength and puncture resistance can help in the assessment of protective performance.

Property	Test Method	Typical Result	EN
Abrasion Resistance ⁷	EN 530 Method 2	>100 cycles	2/6 ¹
Basis Weight	DIN EN ISO 536	41.5 g/m ²	N/A
Colour	N/A.	White	N/A
Exposure to high Temperature	N/A.	Melting point ~135 °C	N/A
Flex Cracking Resistance 7	EN ISO 7854 Method B	>100000 cycles	6/6 ¹
Puncture Resistance	EN 863	>10 N	2/6 ¹
Resistance to water penetration	AATCC 127	>10 kPa	N/A
Surface Resistance at RH 25%, inside ⁷	EN 1149-1	< 2,5 • 10 ⁹ Ohm	N/A
Surface Resistance at RH 25%, outside ⁷	EN 1149-1	< 2,5 • 10 ⁹ Ohm	N/A
Tensile Strength (MD)	DIN EN ISO 13934-1	>60 N	2/6 ¹
Tensile Strength (XD)	DIN EN ISO 13934-1	>60 N	2/6 ¹
Trapezoidal Tear Resistance (MD)	EN ISO 9073-4	>10 N	1/6 ¹
Trapezoidal Tear Resistance (XD)	EN ISO 9073-4	>10 N	1/6 ¹

1 According to EN 14325 2 According to EN 14126 3 According to EN 1073-2 4 According to EN 14116 12 According to EN 11612 5 Front Tyvek ® / Back 6 Based on test according to ASTM D-572 7 See Instructions for Use for further information, limitations and warnings > Larger than < Smaller than <= Smaller than or equal to N/A Not Applicable STD DEV Standard Deviation

COMFORT



The comfort of a protective garment during use is largely determined by its weight, its permeability to vapour and air (breathability) and insulating properties. Data on these attributes is provided according to test method and, as with other data, can be compared by garment.

Property	Test Method	Typical Result	EN
Air Permeability (Gurley method)	TAPPI T460	< 45 s	N/A

2 According to EN 14126 5 Front Tyvek ® / Back > Larger than < Smaller than <= Smaller than or equal to N/A Not Applicable

BIOLOGICAL BARRIER



Detailed information on the protective performance (resistance to penetration) of DuPont clothing when exposed to biologically contaminated aerosols, liquids and dusts as well as blood, body fluids and blood-borne pathogens. Sorted by relevant European standard.

Property	Test Method	Typical Result	EN
Resistance to Penetration by Biologically Contaminated Aerosols	ISO/DIS 22611	1 < log ratio < 3	1/3 ²
Resistance to Penetration by Blood and Body Fluids using Synthetic Blood	ISO 16603	3,5 kPa	3/6 ²
Resistance to Penetration by Blood-borne Pathogens using Bacteriophage Phi-X174	ISO 16604 Procedure C	1,75 kPa	2/6 ²
Resistance to Penetration by Contaminated Liquids	EN ISO 22610	<u><</u> 15 min	1/6 ²
Resistance to Penetration by Contaminated Solid Particles	ISO 22612	2 < log cfu < 3	1/3 ²

2 According to EN 14126 > Larger than < Smaller than <= Smaller than or equal to

PENETRATION AND REPELLENCY



A specific test method, EN ISO 6530, is used to measure the indexes of penetration, absorption and repellency of protective clothing material exposed to liquid chemicals. Results listed here reflect the penetration resistance and repellency of DuPont fabrics to 30% sulphuric acid and 10% sodium hydroxide.

Property	Test Method	Typical Result	EN
Repellency to Liquids, Sodium Hydroxide (10%)	EN ISO 6530	>95 %	3/3 ¹
Repellency to Liquids, Sulphuric Acid (30%)	EN ISO 6530	>95 %	3/3 ¹
Resistance to Penetration by Liquids, Sodium Hydroxide (10%)	EN ISO 6530	<1 %	3/3 ¹
Resistance to Penetration by Liquids, Sulphuric Acid (30%)	EN ISO 6530	<1 %	3/3 ¹

1 According to EN 14325 > Larger than < Smaller than <= Smaller than or equal to

GARMENT PERFORMANCE



Information relating to the protective performance of a garment according to European standards where applicable. Includes important characteristics such as protection against radioactive contamination, seam strength and shelf life. Inward leakage and resistance to penetration by liquids, according to the relevant Type classification, are also detailed.

Property	Test Method	Typical Result	EN
Nominal protection factor ⁷	EN 1073-2	>50	2/3 ³
Seam Strength	EN ISO 13935-2	>75 N	3/6 ¹
Shelf Life ⁷	N/A.	10 years ⁶	N/A
Type 5: Inward Leakage ¹¹	EN ISO 13982-2	1 %	N/A
Type 5: Inward Leakage of Airborne Solid Particulates	EN ISO 13982-2	Pass	N/A
Type 6: Resistance to Penetration by Liquids (Low Level Spray Test)	EN ISO 17491-4, Method A	Pass	N/A

1 According to EN 14325 3 According to EN 1073-2 12 According to EN 11612 13 According to EN 11611 5 Front Tyvek ® / Back 6 Based on test according to ASTM D-572 7 See Instructions for Use for further information, limitations and warnings 11 Based on the average of 10 suits, 3 activities, 3 probes > Larger than < Smaller than <= Smaller than or equal to N/A Not Applicable * Based on lowest single value

WARNING

- The garment does not protect against ionizing radiation.
- The information provided herein corresponds to our knowledge on the subject at the date of its publication. This information may be subject to revision as new knowledge and experience becomes available. The data provided fall within the normal range of product properties and relate only to the specific material designated; these data may not be valid for such material used in combination with any other materials or additives or in any process, unless expressly indicated otherwise. The data provided should not be used to establish specification limits or used alone as the basis of design; they are not intended to substitute for any testing you may need to conduct to determine for yourself the suitability of a specific material for your particular purposes. Since DuPont cannot anticipate all variations in actual end-use conditions DuPont makes no warranties and assumes no liability in connection with any use of this information. Nothing in this publication is to be considered as a license to operate under or a recommendation to infringe any patent rights.
- This garment and/or fabric are not flame resistant and should not be used around heat, open flame, sparks or in potentially flammable environments.

PERMEATION DATA



Permeation is the process by which a solid, liquid or gaseouses chemical moves through a protective clothing fabric at a molecular level. Permeation data assist in the selection of the most appropriate protective garment for a particular application and in the estimation of how long it can be safely worn. Standardised test methods are used to determine the resistance of DuPont materials to permeation, the results of which can be selected according to a specific chemical, chemical class or fabric.

Hazard / Chemical Name	Physical State	CAS	BT Act	ВТ 0.1	BT 1.0	EN	SSPR	MDPR	Cum 480	Time 150	ISO
Acetic acid (30%)	Liquid	64-19-7	imm	imm	imm		13.5	0.001			
Ammonium hydroxide (16%)	Liquid	1336-21- 6	imm	imm	imm		20.3	0.005			
Ammonium hydroxide (28% - 30%)	Liquid	1336-21- 6	imm	imm	imm		16.7	0.014			
Carboplatin (10 mg/ml)	Liquid	41575- 94-4	>240	>240	>240	5	<0. 001	0.001			
Carmustine (3.3 mg/ml, 10 % Ethanol)	Liquid	154-93-8	imm	imm	>240	5	<0.3	0.001			
Caustic ammonia (16%)	Liquid	1336-21- 6	imm	imm	imm		20.3	0.005			
Caustic ammonia (28% - 30%)	Liquid	1336-21- 6	imm	imm	imm		16.7	0.014			
Caustic soda (10%)	Liquid	1310-73- 2	>240	>480	>480	6	<0. 005	0.005			
Caustic soda (40%)	Liquid	1310-73- 2	imm	>30	>240	5	<0. 005	0.005			
Caustic soda (50%)	Liquid	1310-73- 2	imm	>30	>240	5	0.85	0.01			
Caustic soda (>95%, solid)	Solid	1310-73- 2	>480	>480	>480	6	<0.01	0.01			
Cisplatin (1 mg/ml)	Liquid	15663- 27-1	>240	>240	>240	5	<0. 0002	0.0002			
Cyclo phosphamide (20 mg/ml)	Liquid	50-18-0	>240	>240	>240	5	<0. 002	0.002			
Dimethyl sulfate	Liquid	77-78-1	imm	imm	imm		>160	0.02			
Doxorubicin HCl (2 mg/ml)	Liquid	25136- 40-9	>240	>240	>240	5	<0. 003	0.003			
Ethane 1,2-diol	Liquid	107-21-1	imm	imm	imm		6.6	0.002			
Ethylene glycol	Liquid	107-21-1	imm	imm	imm		6.6	0.002			
Etoposide (Toposar®, Teva) (20 mg/ml, 33.2 % (v /v) Ethanol)	Liquid	33419- 42-0	>240	>240	>240	5	<0.01	<0.01			
Fluorouracil, 5- (50 mg/ml)	Liquid	51-21-8	imm	imm	>30	2	na	0.001			
Formic acid (30%)	Liquid	64-18-6	imm	imm	imm		nm	0.001			

Ganciclovir (3 mg/ml)	Liquid	82410- 32-0	>240	>240	>240	5	<0. 005	0.005		
Gemcitabine (38 mg/ml)	Liquid	95058- 81-4	imm	>60	>240	5	<0.4	0.005		
Glycerine	Liquid	56-81-5	>240	>480	>480	6	0.03	0.01		
Glycerol	Liquid	56-81-5	>240	>480	>480	6	0.03	0.01		
Glycol alcohol	Liquid	107-21-1	imm	imm	imm		6.6	0.002		
Hydrochloric acid (16%)	Liquid	7647-01- 0	imm	imm	imm		na	0.05		
Hydrochloric acid (32%)	Liquid	7647-01- 0	imm	imm	imm		na	0.05		
Hydrogen peroxide (10%)	Liquid	7722-84- 1	>10	>10	>480	6	<0.01	0.01		
Hydrogen peroxide (30%)	Liquid	7722-84- 1	imm	imm	imm		>0.11	0.04		
lfosfamide (50 mg/ml)	Liquid	3778-73- 2	imm	imm	>240	5	<0.5	0.003	>480	6

Hazard / Chemical Name	Physical State	CAS	BT Act	ВТ 0.1	ВТ 1.0	EN	SSPR	MDPR	Cum 480	Time 150	ISO
Irinotecan (20 mg/ml)	Liquid	100286- 90-6	imm	>240	>240	5	<0.1	0.0028			
Methotrexate (25 mg/ml, 0.1 N NaOH)	Liquid	59-05-2	>240	>240	>240	5	<0.001	0.001			
Mitomycin (0.5 mg/ml)	Liquid	50-07-7	>240	>240	>240	5	<0. 0009	0.0009			
Nicotine (9 mg/ml)	Liquid	54-11-5	>480	>480	>480	6	<0.08	0.08			
Nitric acid (10%)	Liquid	7697-37-2	>60	>120	>480	6	na	0.05		>477	5
Nitric acid (30%)	Liquid	7697-37-2	imm	imm	imm		4.6	0.001			
Oxaliplatin (5 mg/ml)	Liquid	63121-00- 6	imm	imm	imm		na	0.006			
Paclitaxel (Hospira) (6 mg/ml, 49.7 % (v/v) Ethanol)	Liquid	33069-62- 4	>240	>240	>240	5	<0.01	<0.01			
Phosphoric acid (50%)	Liquid	7664-38-2	>480	>480	>480	6	<0.05	0.05			
Potassium chromate (sat)	Liquid	7789-00-6	>480	>480	>480	6	<0.005	0.005			
Potassium hydroxide (40%)	Liquid	1310-58-3	imm	imm	>30	2	0.7	0.001			
Propane -1,2,3-triol	Liquid	56-81-5	>240	>480	>480	6	0.03	0.01			
Sodium acetate (sat)	Liquid	127-09-3	imm	>480	>480	6	<0.1	0.05		>480	6
Sodium chloride (9 g/l)	Liquid	7647-14-5	>240	>240	>240	5	<0.02	0.02			
Sodium hydroxide (10%)	Liquid	1310-73-2	>240	>480	>480	6	<0.005	0.005			
Sodium hydroxide (40%)	Liquid	1310-73-2	imm	>30	>240	5	<0.005	0.005			
Sodium hydroxide (50%)	Liquid	1310-73-2	imm	>30	>240	5	0.85	0.01			
Sodium hydroxide (>95%, solid)	Solid	1310-73-2	>480	>480	>480	6	<0.01	0.01			
Sodium hypochlorite (10-15 % active chlorine)	Liquid	7681-52-9	>240	>240	>480	6	<0.6	0.05			
Sodium hypochlorite (5.25-6%)	Liquid	7681-52-9	>480	>480	>480	6	<0.025	0.025			
Sulfuric acid (18%)	Liquid	7664-93-9	>240	>240	>480	6	<0.05	0.05			
Sulfuric acid (30%)	Liquid	7664-93-9	>10	>240	>240	5	<0.05	0.05			
Sulfuric acid (50%)	Liquid	7664-93-9	imm	>30	>60	3	38	0.01			
Sulfuric acid dimethyl ester	Liquid	77-78-1	imm	imm	imm		>160	0.02			
Thiotepa (10 mg/ml)	Liquid	52-24-4	imm	imm	imm		na	0.001			
Vincristine sulfate (1 mg/ml)	Liquid	2068-78-2	>240	>240	>240	5	<0.001	0.001			
Vinorelbine (0.1 mg/ml)	Liquid	71486-22- 1	>240	>240	>240	5	<0. 0209	0.00209			

Important Note.

SPECIAL WARNINGS

- *Serged and bound seams are degraded by some hazardous liquid chemicals, such as strong acids, and should not be worn when these chemicals are present.
- *Liquid barrier performance varies based on the amount of liquid that may get on the garment, the length of time the liquid is on the garment, applied pressure and certain physical properties of the liquid. Tyvek®400, Tyvek® 400 D, ProShield®, ProShield® 10, ProShield® 60, Tyvek® 400 FC, and ProShield® 70 garments are not appropriate if during use they are getting wet (liquid is dripping or running, or it is wet to the touch) or if spotting is observed on skin or garments worn under the protective garment. Tyvek® 500 and Tyvek® 600 offer improved liquid barrier, but may not be appropriate if spotting is observed on the skin or garments worn under the protective garment. In applications where a higher liquid barrier is needed, consider Tychem® 2000 and Tychem® 4000 garments with taped seams.
- Tyvek® 500 products manufactured before January 2023 did contain natural rubber latex which may cause allergic reactions in some sensitized individuals. Anyone who begins to exhibit an allergic response during the use of DuPont products should immediately cease using these products. The incident should also be reported to DuPont at +1 (888) 439-2988 so that an investigation can be initiated.
- **Garments made using Tyvek® 400, Tyvek® 500, Tyvek® 600 and Tyvek® 800 fabrics will burn and possibly melt. None of
 these garments should be worn near heat, open flames, sparks or any other possible ignition source nor should they be
 worn in potentially explosive or flammable environments. If these garments do burn or melt while being worn, it may
 increase the severity of burn injuries even when worn over garments which are flame resistant, including, but not limited to,
 Nomex® IIIA or Nomex® Comfort garments.
- *CAUTION: This information is based upon technical data that DuPont believes to be reliable. It is subject to revision as additional knowledge and experience are gained. DuPont makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics, not complete garments, under controlled conditions. It is intended for informational use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact DuPont for specific data. If fabric becomes torn, abraded or punctured, or if seams or closures fail, or if attached gloves, visors, etc. are damaged, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including, without limitation, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of DuPont or others covering any material or its use.

Cellosolve® and Selexol[™] are registered trademarks of Dow Chemicals Company. Skydrol® is a registered trademark of Solutia.

Tyvek® 500, Tyvek® 600, Tyvek® 800 products manufactured before January 2023 did contain natural rubber latex which
may cause allergic reactions in some sensitized individuals. Anyone who begins to exhibit an allergic response during the
use of DuPont products should immediately cease using these products. The incident should also be reported to DuPont at
+1 (888) 439-2988 so that an investigation can be initiated.